

Typ	Zapalování		Ø trysky	Spotřeba	Doba provozu		Hmotnost	Vhodné kartuše doporučené výrobcem	Výkon
	Manual	Piezo			mm	g/h		MIN	
1040A		*	0,25	105	1h50'/2h10'	5h50'/6h10'	410	1120S-1121F	1,37
1045A	*		0,25	105	1h50'/2h10'	5h50'/6h10'	400	1120S-1121F	1,37
820A		*	0,25	105	1h50'/4h45'/3h10'	5h30'/8h/7h10'	310	1121F-1126F46F-575 (580)	1,37
825A	*		0,25	105	1h50'/4h45'/3h10'	5h30'/8h/7h10'	300	1121F-1126F46F-575 (580)	1,37
955	*		0,17	62	3h/3h40'	7h/7h40'	330	1120S-1121F	0,85
820AKIT		*	0,25	105	3h10'	7h10'	310	575	1,37
KE2018	*		0,25	105	1h50'	5h50'	372	1120S	1,37
KE2019		*	0,25	105	1h50'	5h50'	382	1120S	1,37
770		*	0,25	105	1h50'	5h50'	548	1120S	1,37
775	*		0,25	105	1h50'	5h50'	538	1120S	1,37
1217C	*		0,35	120	1h35'	4h30'	989	1120S	2,2
1217S	*		0,35	120	1h35'/1h54'/2h45'	4h30'/5h/5h40'	989	1121F-1126F46F-575 (580)	2,2
1047	*		0,28	114	2h/4h23'/2h53'	5h/7h23'/5h53'	182	1121F-1126F46F-575 (580)	1,75
1060		*	0,28	114	2h/4h23'/2h53'	5h/7h23'/5h53'	187	1121F-1126F46F-575 (580)	1,75
1059		*	0,22	110	2h10'	6h15'	155	577	1,37
1064E		*	0,35/0,14	265/45	1h27'/8h33'	5h50'/16h40'	704	581	3,67/0,62
1062E		*	0,35	254	1h31'	5h30'	481	581	3,46